



Datasheet

PUR 25m Long transparent Flexible Tube Reinforced, 82mm Bend Radius, Applications Various

RS Stock number 339-6297



CPR SERIES

A polyurethane hose with outstanding elasticity providing excellent flexibility and kink-resistance, even in extreme cold conditions.

KEY FEATURES:

- | Ultra-flexible in low temperature environments.
- | Exceptional abrasion resistance.
- | Resistant to a wide range of chemicals.
- | Compliant with F&DA regulations.
- | Excellent clarity for clear visibility.
- | High levels of kink resistance and good memory.
- | 85 Shore A hardness.
- | Service Temperature -40°C to + 65°C.

SIZES:

- | Available in 30m coils
- | 6mm - 25mm ID

COLOURS:

- | Clear

APPLICATION EXAMPLES:

- | Conveyance of gases, liquid, dry powders and granules (especially where good abrasion characteristics are required).