

760RWK DIGITAL SOLDERING & HOT AIR REWORK STATION

- TC50A Industrial grade Soldering iron (50W)
- Temperature controlled
- Digital temperature display
- Push button range adjustable from 200°C - 450°C
- Sensor close to tip for fast response times
- Iron plated, nickel coated bits for long life
- Upto 30,000 operations tip life
- 9 replacement tips in range
- Burnproof Silicone cable fitted as standard
- Robust metal enclosure
- LED temperature indication
- Power on indication
- Iron voltage 24V
- ST6A stand included
- 2 x Hot-Air nozzles included
- Station switchable between Soldering and Hot air control



SPECIFICATION - STATION

Voltage	230VAC
Temperature	200°C - 450°C
Stability	+/- 2°C No load
Temp rise time (350°C)	55 secs
Power	50W
Leakage current	2.0 μ A
Fitted bit	1100 (2.3mm)
Cable type	Silicone
Cable Length	1.5 mtr
Plug	UK, EU
Dims (Tip to handle)	182mm

SPECIFICATION – HOT AIR REWORK

Power max	700W
Temperature	100°C - 500°C
Handle length	240mm
Handle weight	180g

- Manufactured to Din EN 60335-2-45
- CE & EMC Low Voltage directive conformity
- Easy change shimmed bits
- Fume extraction kit available separately



Replacement Bits - 1100 series



Replacement Nozzles



Safety Stand ST6A