

# rotronic

**Datenblatt - Fiche technique - Data sheet**

**11.04.5660**




**ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 10m**

**ROLINE Câble écran HD15 M/M avec noyaux de ferrite + DDC,  
10 m**

**ROLINE High Quality VGA Cable with Ferrite + DDC,  
HD15 M – HD15 M, 10 m**


# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE



**NOTE:**

- CABLE: UL-2919 28AWG(7/0.127 T.C)\*3COAX(75 OHMS) +24AWG(7/0.20 T.C)\*9C+AL/MY+D.W+BRAID(85%) PVC JACKET, COLOR: BLACK(NK-K01) OD:  $\varnothing$  8.5 $\pm$ 0.15mm, (C2919355-1) (SPACE SHUTTLE)
- CONNECTOR:  
P1&P2:HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- ELECTRICAL TEST: <1>.100% OPEN SHORT & MIS WIRE TEST  
<2>. CONTACT RESISTANCE 3 Ohms MAX  
<3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING: <1>EACH PC / POLYBAG + BIG HEADER CARD + BAR CODE LABEL.  
<2>EACH PC / POLYBAG + BAR CODE LABEL.



Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Title		HDB15/M-HDB15/M W/FERRITE CORES CABLE	
Customer P/N			

**Rotronic co., LTD.**

DWG	P/N	LFT(mm)	BAR CODE NO.	PACKING	CTN BAR CODE
120-3272-3	11.04.5670	20000±200	7611990192267	<2>	7611990992263
120-3272-2	11.04.5660	10000±100	7611990192250	<2>	7611990992256
120-3272-1	11.04.5653	3000±30	7611990192243	<1>	7611990992249

Drawn	FANNIE 09/24/10'	Customer P/N	
Check		App'd	
Engr		Scale	NONE
		Units	m/m
		Dwg No.	120-3272
		REV.	A
		Sheet	1/1