

MB10/10.L3



Products Low Voltage Products and Systems Connection Devices Terminal Blocks Solution Series

General Information

Extended Product Type:	MB10/10.L3
Product ID:	1SNA115329R2400
EAN:	3472591153293
Catalog Description:	MB10/10.L3 Distribution Terminal Blocks
Long Description:	MB10/10.L3 Distribution Terminal Blocks - Grey,10mm ² RatedCrossSection, 32.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail.

Additional Information

ABB Industrial IT Suite:	Control IT
Color:	grey
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160001C0207-CH-G Distribution terminals
Declaration of Conformity - CE:	1SND225007U1000
EAC Certificate:	1SND161009A1100
EAN:	3472591153293
ETIM 4:	EC001894 - Distributor assembly terminal blocks
ETIM 5:	EC001894 - Distributor assembly terminal blocks
ETIM 6:	EC001894 - Distributor assembly terminal blocks
Environmental Information:	1SND220038E1002
Flammability According to UL94:	V2
Function:	Distribution
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160001C0207-CH-G Distribution terminals
Invoice Description:	MB10/10.L3 Distribution Terminal Blocks
Minimum Order Quantity:	5 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	5 piece
Package Level 1 EAN:	3472591153293
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 Height:	48 mm
Package Level 1 Length:	120 mm
Package Level 1 Units:	5 piece
Package Level 1 Width:	77 mm
Package Level 2 Gross Weight:	8.75 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	140 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	6720 piece

Package Level 3 Units:	0/20 piece
Pollution Degree:	2
Product Main Type:	MB10/10
Product Name:	Terminal Block
Product Net Depth:	40.5 mm
Product Net Height:	44.5 mm
Product Net Weight:	60 g
Product Net Width:	32.5 mm
Product Packing Type:	Box
Rated Cross-Section:	10 mm ²
Rated Impulse Withstand Voltage (U _{imp}):	8 kV
Recommended Screw Driver:	5.5 mm
RoHS Information:	1SND230023F0202
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	grey Distribution Terminal Blocks MB10/10.L3
Spacing:	10 mm
Sub-Function:	Phases
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
Wire Stripping Length:	12 mm

