
8065266 DFPD-900-RP-90-RS60-F14 Semi-rotary drive - Series: All



8065266 DFPD-900-RP-90-RS60-F14 Semi-rotary drive - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	8229257	DFPD-900-.. REV1 Set of wearing parts	Spare parts: 3, 5, 8, 9, 10, 14, 16, 17, 19, 21, 22, 23, 24, 25, 27, 28, 30, 31 Replacing the wearing parts Attention, please order position 32 as well	1	PC
1		ISO 4017-M12X45-A2-70 Hexagon head screw	Not available Tightening torque 65 Nm / 47.9 lbf ft	8	PC
2		ISO 7092-12-200HV-A2 Disc	Not available	8	PC
3		DIN 6797-J-13-A2-70 Toothed disc	Not available separately, see position 6+7+999	8	PC
4		DFPD-900-D/S End cap	Not available	2	PC
5		183,74X3,53-N-NBR70 O-ring	Not available separately, see position A	2	PC
6	8070317	DFPD-900-.S-1-../T6 Spring module		1	PC
7	8070325	DFPD-900-.S-12-../T6 Spring module		1	PC
8		DFPD-900-../T6 Slip ring	Not available separately, see position A Repair note: Slip_ring	2	PC
9		164,47X6,99-N-NBR70 O-ring	Not available separately, see position A	2	PC
10		DFPD-900-../T6 Slide element	Not available separately, see position A	2	PC
11		DFPD-900-90 Piston	Not available Lubricate with SYNTHY POLYMER 402/2 during assembly	2	PC
12		DFPD-700/900 Plug	Not available	2	PC
13		ISO 4762-M5X16-A2-70 Socket head screw	Not available Tightening torque 7 Nm / 5.2 lbf ft	2	PC
14		J-5,1-A2-70 Toothed disc	Not available separately, see position A	2	PC
15		DFPD-700/900-AN Sub-base	Not available	1	PC
16		B-21X2-N-NBR70 O-ring ISO3601	Not available separately, see position A	2	PC
17		DIN 471-48X1,75-A2 Retaining ring	Not available separately, see position A	1	PC
18		DIN 988-48X60X2-A2 Shim	Not available	1	PC
19		DFPD-900-../T6 Slip ring	Not available separately, see position A Repair note: Slip_ring	1	PC
20		DFPD-900-90-F1012-AN Housing	Not available Lubricate with SYNTHY POLYMER 402/2 during assembly	1	PC
21		B-15,47X3,53-N-NBR70 O-ring ISO3601	Not available separately, see position A	2	PC
22		16,3X30X5-1.4301 Ring	Not available separately, see position A	2	PC
23		ISO 4032-M16-A2-70 Hex nut	Not available separately, see position A Tightening torque 177.5 Nm / 130.9 lbf ft	2	PC
24		DFPD-900/1200 adjusting screw	Not available separately, see position A	2	PC
25		DFPD-900-../T6 Slip ring	Not available separately, see position A Repair note: Slip_ring	1	PC

Pos.	Part no.	Type	Note	Qty.	Unit
26		DFPD-900-90 Cam	Not available	1	PC
27		B-40,87X3,53-N-NBR70 O-ring ISO3601	Not available separately, see position A	1	PC
28		DFPD-900-../T6 Slip ring	Not available separately, see position A Repair note: Slip_ring	1	PC
29		DFPD-900-KT27 Shaft	Not available Lubricate with SYNTHY POLYMER 402/2 during assembly	1	PC
30		DFPD-900-../T6 Slip ring	Not available separately, see position A Repair note: Slip_ring	1	PC
31		B-66,27X3,53-N-NBR70 O-ring ISO3601	Not available separately, see position A	1	PC
32	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease	Not included in wearing-parts kit	2	PC