



ENGLISH

Datasheet

RS Pro Tap Wrenches: T-Bar Type

Non Ratchet Type

RS Stock No: 444-908



Specifications:

Non Ratchet Type

Fixed T-handle

Hardened & tempered split collet chucks for positive grip

Knurled & hardened clamping nut

Handle: 125mm

Height: 92mm

A/F range: 5-7mm

Order Code	Manufacturers Code	Description
444-908	4300-231	Tap Wrenches: T-Bar Type



ENGLISH

Datasheet

RS Pro Tap Wrenches: T-Bar Type

Non Ratchet Type

Tap Range:

Square	ISO 529	ISO 529	DIN 352	ISO 529	ISO 529	ISO 529	ISO 529	ISO 529	ANSI
Dimensions	Metric Coarse	Metric Coarse	Metric Coarse	BSW	BSF	UNC	UNF	BA	NPT
	Full Diameter	Relieved Shank							
	Shank with Recess								
Size mm	Size	Size	Size	Size	Size	Size	Size	Size	Size
5	M6	M8	M6	1/4	1/4	1/4	1/4		
5.6	M7	M9							
5.9									1/16
6			M7						
6.3	M8	M10, M11		5/16, 7/16	5/16, 7/16	5/16, 7/16	5/16, 7/16		
6.8			M8						
7.1	M9	M12		1/2	1/2	1/2	1/2		