

Datasheet

RS Pro 9684641 Analogue Positive Pressure Gauge Bottom Entry 60psi, Connection Size G 3/8 RS Calibration RS Stock No: **342-5749**



Product Details

RS Pro analogue positive pressure gauge bottom entry has a maximum pressure measurement of 60 psi with connection size of G 3/8. A general purpose gauge is suitable for all gaseous and liquid media that will not destruct the pressure system or attack copper alloy parts.

Features and Benefits

- Instrument glass window
- Inbuilt restrictor screw
- Copper alloy element and movement
- Stainless steel case with G 3/8 Inch BSPM (32 mm flats)
- Bottom entry connection
- Ambient operating temperature between -20 and +60°C
- Operating temperature of +60°C
- 1.6 Per DIN 16005 accuracy class
- Calibrated versions available



ENGLISH

Specifications:

Calibrated	RSCAL
Case Material	Stainless Steel
Connection Size	BSP G 3/8
Gauge Outside Diameter	100 mm
Maximum Operating Temperature	+60°C
Maximum Pressure Measurement	60 psi
Minimum Operating Temperature	-40°C
Minimum Pressure Measurement	0 psi
Pressure Gauge Type	Bottom Entry
Suitable For	Liquid, Gas