

**FAG****6219-2Z-C3**

Deep groove ball bearing

Deep groove ball bearing 62...-2Z, single row, shields, steel sheet metal cage

Technical information



Your current product variant

Sealing	2Z	Non-contact shield on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	95 mm	Bore diameter
D	170 mm	Outside diameter
B	32 mm	Width
C _r	116,000 N	Basic dynamic load rating, radial
C _{0r}	82,000 N	Basic static load rating, radial
C _{ur}	4,800 N	Fatigue load limit, radial
n _G	4,550 1/min	Limiting speed
n _{gr}	4,950 1/min	Reference speed
≈m	2.73 kg	Weight



Mounting dimensions

$d_{a\ min}$	107 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	158 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	2.1 mm	Minimum chamfer dimension
D_1	146.72 mm	Shoulder diameter outer ring
D_2	150.86 mm	Caliber diameter outer ring
d_1	118.3 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	14.5	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides