

# WT-BASE HF 9 BK - Cable binder base



3240705

<https://www.phoenixcontact.com/gb/products/3240705>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binder base, for cable binders up to 9 mm wide, screwable, 5 mm fixing hole, 2-sided cable binder feed-through

## Commercial data

Item number	3240705
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE713Z
Product key	BE713Z
Catalog page	Page 622 (C-3-2019)
GTIN	4046356703925
Weight per piece (including packing)	1.56 g
Weight per piece (excluding packing)	1.05 g
Customs tariff number	39269097
Country of origin	IT

# WT-BASE HF 9 BK - Cable binder base



3240705

<https://www.phoenixcontact.com/gb/products/3240705>

## Technical data

### Product properties

Product type	Cable tie
Type	Fixing
Tensile strength GRP	700 N

### Dimensions

Width	14.6 mm
Height	11 mm
Length	22.5 mm
Hole diameter	5 mm
Diameter mounting hole	5 mm

### Internal dimensions

Width_inside	9 mm
--------------	------

### Material specifications

Color	black (RAL 9005)
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Cable/line

Tensile strength	700 N
------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

### Mounting

Mounting type	Screw mounting
---------------	----------------

# WT-BASE HF 9 BK - Cable binder base



3240705

<https://www.phoenixcontact.com/gb/products/3240705>

## Classifications

### ECLASS

ECLASS-13.0	23159090
-------------	----------

### ETIM

ETIM 9.0	EC011571
----------	----------

### UNSPSC

UNSPSC 21.0	39121700
-------------	----------

# WT-BASE HF 9 BK - Cable binder base



3240705

<https://www.phoenixcontact.com/gb/products/3240705>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)