

FEATURES

- **2 m cable length:** Provides flexibility and reach for connecting devices at a distance.
- **IEC C19 to BS 1363/A connectors:** Ensures compatibility with a wide range of equipment and power sources.
- **13 A current rating:** Supports high-power devices safely.
- **250 V voltage rating:** Suitable for standard electrical systems.
- **Black PVC jacket:** Offers durability and protection against environmental factors.
- **Straight mains socket type:** Facilitates easy and straightforward connections.

RS PRO 2 m Power Cable, IEC C19 to BS 1363/A

RS Stock No: 558-976



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable and efficient power transfer in various electrical applications. With a length of 2 metres, it connects devices with an IEC C19 connector to a BS 1363/A mains socket, making it ideal for use in both commercial and residential settings. The cable supports a current rating of 13 A and a voltage of 250 V, ensuring safe and effective power delivery.

General Specifications

Connector Type A	IEC C19
Connector Type B	BS 1363/A
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

Mechanical Specifications

Cable Length	2 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	13 A
Voltage	250 V

Approvals

Standards/Approvals	ASTA, CCCs, CSA, EAC, ENEC 11, ICC, JET, PSE, R31947, RCM N10544, Singapore Safety Mark, UL
---------------------	---

