



Classic filament LEDbulbs

CLA LEDBulb D 8-60W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

| General Information | |
|---------------------------------------|---------------------|
| Cap-Base | B22 [B22] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle | 20000X |
| Technical Type | 8-60W |
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Luminous Flux (Nom) | 806 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 100.00 lm/W |
| Color Consistency | <6 |
| Color Rendering Index (Nom) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Nom) | 8 W |

| Lamp Current (Nom) | 52 mA |
|---------------------------------|-----------|
| Wattage Equivalent | 60 W |
| Starting Time (Nom) | 0.5 s |
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.7 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 55 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Approval and Application | |
| Energy Efficiency Label (EEL) | A+ |
| Energy Consumption kWh/1000 h | 8 kWh |


Classic filament LEDbulbs

Product Data

| | |
|-------------------------------|------------------------------------|
| Full product code | 871869670946700 |
| Order product name | CLA LEDBulb D 8-60W A60 B22 827 CL |
| EAN/UPC - Product | 8718696709467 |
| Order code | 929001331302 |
| Numerator - Quantity Per Pack | 1 |

| | |
|---------------------------------|--------------|
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 929001331302 |
| Net Weight (Piece) | 0.030 kg |


Dimensional drawing




Bulb A60 230V7.5-60W 806lm 2700K D Clear

| Product | D | C |
|------------------------------------|-------|--------|
| CLA LEDBulb D 8-60W A60 B22 827 CL | 60 mm | 102 mm |


Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K




LEDbulb 60W B22 827 CL A60 D




LEDbulb 40W E27 827 CL A60 D

Classic filament LEDbulbs

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

