

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Rotary Hammer with ONECHUCK

PRO GBH 18V-22 X

ONE CHUCK

Power packed, fully in your control

The most important data

Battery voltage	18.0 V
Drilling dia. in concrete with hammer drill bits	4 – 22 mm
Impact rate at rated speed	0 – 4,675 bpm

Part Number 0 611 924 100

Technical data

Technical data

Impact rate at rated speed	0 – 4,675 bpm
Rated speed	0 – 1,050 rpm
Battery voltage	18.0 V
Weight excl. battery	2.6 kg
Tool holder	SDS plus, Cylindrical, HEX
Packaging dimensions (width x length x height)	224 x 349 x 113 mm
Impact energy nominal	2 J

Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 22 mm
Opt. app. range in concrete with hammer drill bits	6 – 12 mm

Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 22 mm
Opt. app. range in concrete with hammer drill bits	6 – 12 mm

Noise/vibration information

Hammer drilling in concrete

Vibration emission value ah	14.7 m/s ²
Uncertainty K	1.5 m/s ²

Chiselling in concrete

Vibration emission value ah	9.6 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- ONECHUCK - A single chuck that can fit SDS-plus, cylindrical and hex drill bits for your wide range of applications
- Dust-free work condition with Auto Power GDE 18V-12 / GDE 12 extractor attachment
- Increased user's protection against accidental jams thanks to KickBack Control
- More holes per charge and continuous power output thanks to motor with constant speed
- Better drilling experience due to Vibration Control, designed to absorb pulsation



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

