



**Part Number :** [191640081](#)  
**Product Description :** Perma-Seal Ring Tongue  
Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Carton  
**Series Number :** 19164  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** SD-651-14

Documents & Resources

**Drawings**  
[191640081\\_sd.pdf](#)  
**Specifications**  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19164
Description	Perma-Seal Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	Perma-Seal
Type	Ring
UPC	800753113657

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	4.492/g
Packaging Type	Carton
Stud Size	1/4" (M6)
Wire Insulation Diameter	9.53mm
Wire Size (AWG)	8
Wire Size mm <sup>2</sup>	8.36

---

### Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for Perma-Seal Terminals and Butt Splices, 8 AWG	<u>640018200</u>