

## FEATURES

- Comprised of tempered chrome vanadium steel and a chemically blackened finish
- The high quality material offers a long life and service
- The keys are precision formed to give an exact dimensional tolerance, to give a precise fit
- The torque, gauge and overall length meet DIN 911 standards
- High torqueing handles provide a firm grip and ease of turning

## RS PRO 10 pieces Hex Key Set, L Shape 1/4in

RS Stock No.: 537-732



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From RS PRO, this short arm hex key set is a handy way to keep differing allen key sizes all in one place. Supplied in a plastic holder, the keys are neatly organized ready for precision work.

The ten-piece key set is corrosion resistant and is made from chrome vanadium steel, for a long and dependable tool life. This convenient and versatile hex key set is ideal for on-the-go hex driver applications.

### General Specifications

|                           |   |
|---------------------------|---|
| <b>Imperial or Metric</b> | Imperial  |
| <b>Number of Pieces</b>   | 10  |
| <b>Shape</b>              | L   |
| <b>Hex Key Type</b>       | Hexagon   |
| <b>Material</b>           | Chrome Vanadium Steel   |
| <b>Finish</b>             | Blackened   |
| <b>Height Safe</b>        | No  |
| <b>Applications</b>       | They are ideal for when fasteners need to be adjusted or equipment needs to be dismantled. From furniture assembly to bicycle maintenance |

### Electrical Specifications

|                     |    |
|---------------------|----|
| <b>Non-Sparking</b> | No |
|---------------------|----|

### Mechanical Specifications

|                          |                                      |
|--------------------------|--------------------------------------|
| <b>Short or Long Arm</b> | Short                                |
| <b>Hardness</b>          | Heat treated hex key to HRC 48 to 52 |

## Dimensions

| Hex Key Size |          |
|--------------|----------|
| Metric       | Imperial |
| 6.35mm       | 1/4in    |
| 1.58mm       | 1/16in   |
| 2.5mm        | 1/8in    |
| 4.76mm       | 3/16in   |
| 2.38mm       | 3/32in   |
| 9.52mm       | 3/8in    |
| 7.93mm       | 5/16in   |
| 3.96mm       | 5/32in   |
| 1.98mm       | 5/64in   |
| 5.56mm       | 7/32in   |

## Approvals

|                           |        |
|---------------------------|--------|
| Compliance/Certifications | DIN911 |
| VDE/1000V Approved        | No     |



