

Features

- Resistant to impact and UV
- Resistant to high and low temperatures
- Nylon lock body
- Heavy steel shackle

RS PRO Padlocks

RS Stock No.: 0217696



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Nylon lock body is resistant to impact, UV, high and low temperature. The shackle is heavy steel chrome plated.

Lock body dimensions: Length 45mm, Width 40mm, Thickness 19mm; Shackle Diameter 6mm, Shackle Height 38mm.

Includes 2 sets lock body warning labels, can write owner's information.

General Specifications

Lock Type	Key
Material	Nylon
Bluetooth	No
Keyed Alike	Keyed to differ
Indoor/Outdoor	Indoor
Weather Proof	No
Colour	Red
Quantity Per Package	1
Packaging Type	Box
Body Shape	Square
Shackle Shape	U
Shackle Material	Steel
Key Retaining	Yes

Mechanical Specifications

Shackle Length	38mm
Body Width	40mm
Shackle Diameter	6mm
Body Thickness	19mm
Vertical Shackle Clearance	38mm
Horizontal Shackle Clearance	20mm

Overall Width	40mm
Body Height	89mm
Weight	74.5g

Approvals

Compliance/Certifications	CE
---------------------------	----