

High-pressure hose, 15 m, ID 8, 315 bar, 2 x EASY!Lock

15 m long high-pressure hose, DN 8, with ANTI!Twist and time-saving EASY!Lock manual screw fitting on both sides.

part number	6.110-030.0
EAN	4054278194424

Technical data

ID (")	ID 8
Temperature (°C)	max. 155
Max. pressure (bar)	315
Length (m)	15
Connection thread	2 x EASY!Lock
Weight incl. packaging (kg)	3,4



15 m high-pressure hose (M 22 x 1.5) with kink protection. With patented rotating AVS trigger gun connector and manual coupling. Further data: DN 8/155°C/315 bar.