

## Features

- **Heavy-Duty Steel Construction** – Engineered from virtually indestructible steel to endure harsh industrial environments.
- **Free-Rotating Design** – Once locked, the device spins freely around the handwheel to prevent unauthorized valve operation.
- **Rising Stem Compatibility** – Features a knockout center to accommodate rising stem valves (OS&Y), expanding usability.
- **Quick Installation** – Tool-free design allows for fast and easy deployment during maintenance or shutdowns.
- **Padlock-Ready Design** – Includes built-in padlock holes; compatible with hasps and multiple padlocks for group lockout.
- **Enhanced Safety Compliance** – Effectively secures gate valves in the off position, supporting lockout/tagout safety protocols.

## RS PRO Metallic Gate Valve Lockout (Fits 165 to 254 mm handle wheel dia.)

RS Stock No.: 0694363



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Metallic Gate Valve Lockout is built for high-performance valve isolation in demanding industrial settings.*
- *Constructed from durable steel, ensuring maximum strength, longevity, and resistance to impact.*
- *Unique rotating mechanism ensures the lockout cannot be removed or tampered with while in use.*
- *Free-Rotating Design – Once locked, the device spins freely around the handwheel to prevent unauthorized valve operation.*
- *Knockout center feature allows compatibility with rising stem (OS&Y) valve types.*
- *Equipped with padlock holes for individual or group lockout using standard LOTO hasps and padlocks.*
- *Designed for quick and easy installation, reducing downtime during lockout procedures.*

## General Specifications

Type	Gate Valve Lockout
Material	Steel
Colour	Red
Padlock Holes	4
Package	PE-LD

## Mechanical Specifications

Outside Dia (A)	266mm
Inside Dia (B)	89mm
Device Width (C)	295mm
Padlock Hole Dia (D)	8.2mm
Device Height (E)	81mm
Weight	1.5 Kgs

## Operation Environment Specifications

Withstand temperature	-40°C to 150°C (-40°F to 302°F)
-----------------------	---------------------------------

