


3302 A-2RS1TN9/MT33


Popular item

Dimensions



d	15	mm
D	42	mm
B	19	mm
d_2	≈ 23.7	mm
D_2	≈ 35.65	mm
$r_{1,2}$	min. 1	mm
a	24	mm

Abutment dimensions



d_a	min.	20.6	mm
d_a	max.	23.5	mm
D_a	max.	36.4	mm
r_a	max.	1	mm

Calculation data

Basic dynamic load rating	C	15.1	kN
Basic static load rating	C_0	9.3	kN
Fatigue load limit	P_u	0.4	kN
Limiting speed		12000	r/min
Calculation factor	k_r	0.07	
Calculation factor	e	0.8	
Calculation factor	X	0.63	
Calculation factor	Y_0	0.66	
Calculation factor	Y_1	0.78	
Calculation factor	Y_2	1.24	

Mass

Mass bearing	0.13	kg
--------------	------	----

