



Datasheet

### 24V neutral white strip led 14,4W – 60 LED per meter

1363584 RS Pro item number – 2,50 meters roll

#### Specifications :

Strip Led for intensive professional usage. Being resin-free, this strip led offers high brightness lighting and delivers a very high power of 980 lumens/m (i.e. approximately 90W/m). Its density of 60 led per meter delivers a homogeneous light on the whole strip length. It's the best choice for a source of main lighting for large surfaces in a professional environment (main hall, restaurant, hotel, meeting room, etc.) or in a private one (salon, living-room).

Warning: being resin-free requires its use to be distant from any source of water spray.

#### Technical Informations :

- Electric consumption / m: 14,4W
- Power / m: 1080 lumens
- Protection: none (IP20)
- Lighting: neutral white 4000K
- Dimension (L x l x h):  
2500 x 10 x 3 mm
- Density of led / m: 60
- Customs Code: 9405403990
- Can be cut every 6 LED



Code color wires connect 24V

- Black + 24V
- Red - white light

LED SMD 5050  
NEUTRAL WHITE