


78 03 125 ESD

Electronic Super Knips® ESD



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precision shaped tips cut wires resting on a board from 0.2 mm dia.
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Cutting edge hardness approx. 54 HRC
- INOX - tool steel





ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	78 03 125 ESD
EAN	4003773011972
Head	polished
Handles	with multi-component grips
Style	0
Pliers	
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities soft wire (diameter) Ø mm	0,2 - 1,6
D mm	7,5
B mm	9,0
A mm	13,5
Length mm	125
Net weight g	55



technical change and errors excepted

