

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hybrid cable, cable length: 1 m, shielded: yes, color of outer sheath: orange RAL 2003



Commercial data

Item number	1623127
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABR
Product key	ABRGCA
Catalog page	Page 118 (C-2-2019)
GTIN	4055626121819
Weight per piece (including packing)	371.7 g
Weight per piece (excluding packing)	314.3 g
Customs tariff number	85444995
Country of origin	DE

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Technical data

Product properties

Product type	Cable by the meter
--------------	--------------------

Connector

Cable specifications

Cable type	HDSLC11Y-J
Transmission speed	CAT5
Transmission speed	100 Mbps (Data interface)
Shielded	yes
Cable structure	(5x 2.5 + 2x (2x 0.5) + (4x 0.34)C) C
External cable diameter	15.50 mm ±0.5 mm
Outer sheath, material	PUR
Material wire insulation	TPE
External sheath, color	orange RAL 2003
Single wire, color	black 1, black 2, black 3, black 4, green/yellow Power wires + PE brown, violet, black 5, green Signal wires blue, yellow, white, orange Data wires
Nominal voltage, cable	1000 V (300 V signal)
Test voltage	4 kV (1.5 kV signal)
Rated current	26 A (Power, in accordance with DIN VDE 0298-4 Tab. 11/5, at 15°C) 8 A (Signal, according to DIN VDE 0298-4 tab. 11/5) 3.6 A (Data, according to DIN VDE 0298-4 tab. 11/5)
Smallest bending radius, fixed installation	73 mm
Smallest bending radius, movable installation	148 mm
Max. bending cycles	1000000
Traversing path	6 m
Acceleration	30 m/s ²
Ambient temperature (operation) for fixed installation	-40 °C ... 80 °C (fixed installation)
Ambient temperature (operation) for flexible installation	-20 °C ... 80 °C (flexible installation)
UL AWM style	20234 / 10492 (80°C/1000 V)
Special properties	Flexible cable conduit capable
Flame resistance	IEC 60332-1-2
Halogen-free	in accordance with EN 50267-2-1
Resistance to oil	EN 60811-2-1

Cable/line

Cable length	1 m
--------------	-----

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1623127>



EAC

Approval ID: 19060508

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Classifications

ECLASS

ECLASS-11.0	27060106
ECLASS-12.0	27060106
ECLASS-13.0	27060106

ETIM

ETIM 9.0	EC003250
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

KC-88014311/1,00 - Hybrid cable



1623127

<https://www.phoenixcontact.com/in/products/1623127>

Accessories

PATG 6/23 - Conductor marker carrier

0808037

<https://www.phoenixcontact.com/in/products/0808037>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, text field height: 4 mm, text field width: 23 mm

PABA WH/23 - Insert label

1013779

<https://www.phoenixcontact.com/in/products/1013779>



Insert label, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, Number of individual labels: 20, text field height: 4 mm, text field width: 23 mm

KC-88014311/1,00 - Hybrid cable




1623127

<https://www.phoenixcontact.com/in/products/1623127>

PABA YE/23 - Insert label

1013782

<https://www.phoenixcontact.com/in/products/1013782>



Insert label, Strip, yellow, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, Number of individual labels: 20, text field height: 4 mm, text field width: 23 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in