

1.12/0

Puller

2-arm pattern

Code	ETIM
8003250	EC002110
EAN	UNSPSC
4036976104387	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Handy robust model for the removal of pulleys, wheels, ball bearings, etc.
- Inexpensive economy model
- The legs grip automatically

Article information

Contents (Qty of pieces)	1	Total length [mm]	125 mm
reversible arms available	no	Total width [mm]	70 mm
Clamping bracket available	no	Total height [mm]	24 mm
Net weight [kg]	0,4 kg	Width of hooked foot [mm]	14 mm
Hook brake available	no	Usable depth of hooked foot d2 [mm]	8 mm
3D data available	no	Thickness of hooked foot at tip	2,0 mm
Spindle anti-slip device	no	Width across flats [mm]	14 mm
Screws included	no	Tractive force (max.) [t]	1
Can be retrofitted with hydraulic spindle	no	Hydraulic spindle optional	-
Usable clamping reach [mm]	80 mm	Number of arms	2
Clamping width (max.) external pulling [mm]	70 mm	automatic pressing	yes
Spindle thread size	M 12x1,5 x 110	reversible hooks	no