

## 1.07/K-2

### Puller-Set

with 9 legs

Code 1676008	ETIM EC011834
EAN 4036976112436	UNSPSC 27-11-17-12
Country of origin Germany	eCl@ss 21-04-15-01
Customs tariff number 82055980	



### Article description

- In plastic case
- Contents: 2 spindles, 1 cross-beam each 2- and 3-arm pattern and 9 slim pulling legs in 3 lengths
- 2. spindle in case 1.07/K saves working time
- 1.07/K-2 both sides with burled inlay

### Article parts list

107/2A03 Cross beam 3-arm 260 mm,106/2A03 Traverse 2-arm 260 mm,106/B-150-S Pull-off hook slim 150 mm (3x),106/5220 Pull-off hook slim 220 mm (3x),106/B-300-S Pull-off hook slim 300 mm (3x),1.2106210 Spindle 22, G 1/2", 210 mm (2x),107/399 Plastic case with foam inlay for 1.07/K-2

### Article information

Contents (Qty of pieces)	<b>10</b>	Anti-slip device on the spindle	<b>no</b>
Version/Execution	<b>with plastic case</b>	Exchangeable spindle tip	<b>no</b>
Graduation	<b>no</b>	Can be retrofitted with hydraulic spindle	<b>no</b>
reversible arms available	<b>no</b>	Clamping width (max.) external pulling [mm]	<b>200 mm</b>
Clamping bracket available	<b>no</b>	Spindle thread size	<b>G 1/2 x 210</b>
Net weight [kg]	<b>13,5 kg</b>	Width of hooked foot [mm]	<b>40 mm</b>
Hook brake available	<b>no</b>	Usable depth of hooked foot d2 [mm]	<b>7 mm</b>
Hook can be moved parallel	<b>no</b>	Thickness of hooked foot at tip	<b>5,0 mm</b>
Quick release lever available	<b>no</b>	Width across flats [mm]	<b>22 mm</b>
3D data available	<b>no</b>	Tractive force (max.) [t]	<b>5,0</b>
Spindle anti-slip device	<b>no</b>	Hydraulic spindle optional	<b>1.06/HSP1</b>
Screws included	<b>no</b>	Usable clamping reach	<b>150 / 220 / 300 mm</b>