


2083 Max. 14,4 W

AC/DC DESKTOP REGULATED

- Max 14,4 W output power
- 230 VAC input voltage
- Available with EU or UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
 - reduced stocking requirements
 - short delivery lead times
 - snap-locks for added safety



Technical specifications	9 V*	9 V*	12 V*	12 V*	24 V
Input voltage:	230 VAC, 50 Hz				
Output voltage:	9VDC	9VDC	12VDC	12VDC	24VDC
Max.output power:	7 W	12 W	10 W	14,4 W	12 W
Load current:	0,8A	1,3A	0,8A	1,2A	0,5A
Temperature range:	-10°C to +40°C				
Protection:	Circuit by thermal fuse in primary				
Insulation class	II				
Electrical safety	EN 60950				
EMC, Emission	EN 61000-6-3				
EMC, Immunity	EN 61000-6-1				
Mains connections:	EU or UK				
Output terminals:	Secondary cable w/snap-on plugs				
Dimensions: UK+EU	81x56x49mm	90x67x59mm	81x56x49mm	90x67x59mm	
Weight: UK+EU	570g	820g	570g	820g	810g

* sec. switch