



List Price \$104.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Actuation	Any Direction
Actuator Action	Momentary
Actuator	Cat Whisker (ZCE06)
Head Type	Wobble Stick
Roller Dimension	n/a
Operating Torque/Force	18.40 Inch-Ounces (0.13Nm)
Maximum Actuation Speed	1 m/s
Lever Arm Length	n/a
Conforming to Standards	CENELEC EN 50047
Type	XCKP
RoHS	Yes
Type of Duty	General Duty
Body Type	Compact Modular (ZCP21)
Shock Resistance	50G
Body Material	Plastic
Vibration Resistance	25G
Connection Type	M12 Connector
Contact Configuration	1 N.O./1 N.C.
Weight	0.198 lbs (0.090kg)
Contact Operation	Snap Action
Positive Opening	No
Terminal Type	Screw Clamp
Ampere Rating	3A
Marketing Trade Name	OsiSense
Maximum Voltage Rating	240VAC/250VDC
NEMA Enclosure Rating	NEMA 1/2/4/6/12/13
Degree of Protection	IP66/67
Approvals	UL Listed - CSA Certified - CE Marked
Operating Temperature Range	-13 to 158°F (-25 to 70°C)

Shipping and Ordering

Category	22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT
----------	---

Generated: 07/13/2010 15:13:02

Discount Schedule	T
GTIN	
Package Quantity	1
Weight	0.21 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.