



DCS387M2

18V XR Compact Reciprocating Saw

Selling Proposition

- Compact saw allows better access to hard to reach cuts
- Improved balance and ease of handling due to central motor position
- Four position blade clamp allows for flush cutting and improved versatility
- Lever action keyless blade clamp for tool-free blade change
- LED for improved visibility of cut

Standard Equipment

- Multi-voltage charger
- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator
- Heavy-Duty TSTAK II Kitbox

Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

| Specifications | |
|---------------------|------------|
| Battery chemistry | XR Li-Ion |
| Voltage | 18 V |
| Battery Capacity | 4.0 Ah |
| Power Output | 610 Watt |
| No Load Stroke Rate | 0-2900 spm |
| Stroke Length | 28.6 mm |
| Weight | 2.3 kg |
| Length | 363 mm |