

CT45 - CT Cut D18 Nitrile Glove

Collection: CT

Range: Hand Protection

Materials: DyUltra™, Polyester, Elastic, Elastane

Dipping:

Inner Pack: 12

Outer Carton: 216

Product information

The premium CT45 cut resistant glove offers exceptional cut level D protection without the use of glass or steel fibres. Coated with Nitrile foam the CT45 offers outstanding grip in wet and dry conditions. The 100% breathable seamless liner offers outstanding comfort for the wearer.

CT

Introducing the Portwest CT collection of cut resistant gloves. State-of-the-art production techniques ensures that these gloves contain no glass or steel fibres while offering excellent levels of cut resistance.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (4X42D)

EN 407: 2020 (X1XXXX)

ANSI/ISEA 105: 2016 CUT Level (A4)



Features

- Level D cut resistance
- 18 gauge liner provides excellent comfort, freedom of movement and superb tactile ability
- Free from glass and steel fibres
- Nitrile foam coating for excellent grip in wet and dry conditions
- Retains cut performance level for up to 10 washes
- Protection against contact heat up to 100°C
- OEKO-TEX® STANDARD 100 approved
- Improved performance
- Breathable seamless liner
- Retail tag which aids presentation for retail sales
- This glove can be used with most mobile touchscreen devices



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

CT45 - CT Cut D18 Nitrile Glove

Commodity Code: 6116102091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/13848-02/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: AB0321/24289-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
CT45G8RXS	Grey/Black	44.0	28.0	42.0	0.0400	0.0517	5036108321735	25036108810462
CT45G8RS	Grey/Black	44.0	28.0	42.0	0.0480	0.0517	5036108321711	25036108810493
CT45G8RM	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321704	25036108810486
CT45G8RL	Grey/Black	44.0	28.0	42.0	0.0600	0.0517	5036108321698	25036108810479
CT45G8RXL	Grey/Black	44.0	28.0	42.0	0.0620	0.0517	5036108321728	25036108810509
CT45G8RXXL	Grey/Black	44.0	28.0	42.0	0.0620	0.0517	5036108321742	25036108810516