

Datasheet

Stock No: 811-4407

RS Pro 5 Core Unscreened White 3185Y Power Cable



Conductors	30/0.25mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation	PVC (Type TI1 to BS 7655)
Insulation Radial	0.7mm
Thickness Diameter over	3.0mm (Nominal)
Insulation Number of	5
Cores	Blue, Brown, Black, Grey & Green/Yellow
Core Colours	
Sheath	PVC (Type TM2 to BS 7655)
Sheath radial thickness	1.3mm
Overall Dimensions	10.7mm (Nominal)
Voltage Rating	300/500V
Conductor Resistance	13.3Ω/km at 20°C (nominal)
Cable Weight	165kg/km (nominal)
Standards	BS EN 50525-2-11 Clause 4.2
Harmonization Code	H05VV-F
Sheath Colour	White
Reel Length	100m