

RS Part Number: **466-172**  
 Specifications and dimensions



- Boxed isolator 3 pole
- ABS plastic enclosure with padlockable handle

Specifications	
Height	125 mm
Width	100 mm
Depth	74 mm
Depth including switch	118 mm
Degree of protection	IP65
Rated operational current Ie AC21A	32 A
Rated operational current Ie AC22A	25 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	15 kW
Rated operational power AC3 440V	11 kW
Maximum gL fuse size IEC	32 A
Rated fused short circuit capacity IEC	30 kA
Knockout size	20 mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm <sup>2</sup>
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	1
Related products	
Main pole contact	<b>136-5281</b>
Neutral contact (early make/late break)	<b>136-5280</b>