

FR50 - Flame Resistant Anti-Static Coverall 350g

Collection: Bizflame™ Plus

Range: Flame Resistant

Shell Fabric: Bizflame Plus: 99% Cotton, 1% Carbon Fibre 350g

Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM² (HAF=82%))

Bizflame™ Plus

BizFlame™ Plus has been developed and designed using a highly innovative flame resistant fabric with added anti-static properties. Constructed from 99% cotton and interwoven with 1% carbon fibres. Excellent tear and tensile strength offer durability while the premium quality cotton fibres give the fabric unrivalled comfort. Inherent anti-static carbon fibre

Flame Resistant

This industry leading flame resistant range provides multi standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement
- Concealed zip pocket
- Available in sizes from XS to 6XL
- Triple-stitched seams for extra durability
- 10 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays



FR50 - Flame Resistant Anti-Static Coverall 350g
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13136-02/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FR50ORRXS	Orange	43.0	28.0	50.0	1.4900	0.0602	5036108187720	15036108674449
FR50ORRS	Orange	43.0	28.0	50.0	1.5700	0.0602	5036108160433	15036108625816
FR50ORRM	Orange	43.0	28.0	50.0	1.5900	0.0602	5036108160440	15036108625809
FR50ORRL	Orange	43.0	28.0	50.0	1.6200	0.0602	5036108160457	15036108625793
FR50ORRXL	Orange	43.0	28.0	50.0	1.7200	0.0602	5036108160464	15036108625823
FR50ORRXXL	Orange	43.0	28.0	55.0	1.7600	0.0662	5036108160471	15036108625830
FR50ORRXXXL	Orange	43.0	28.0	55.0	1.8500	0.0662	5036108160488	15036108625847
FR50ORR4XL	Orange	43.0	28.0	55.0	1.8700	0.0662	5036108182886	15036108625786
FR50ORR5XL	Orange	43.0	28.0	55.0	1.9900	0.0662	5036108217663	15036108704856