

Flat-head Angle Grinder XGT®

GA056G

40Vmax, 125 mm, 3000 - 9000 min⁻¹

Model GA056G is a 125mm flat head angle grinder powered by a 40V Max XGT Li-Ion battery.

Features a Paddle Switch. Reduced access angle at the tip enables excellent workability for deburring in confined or recessed areas. Equipped with a newly designed tool-less wheel cover for flat head angle grinders, allowing access at angles as small as 39°



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	3000 - 9000 min ⁻¹
Disc Diameter	125 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	3,1 - 4,4 kg
Product Dimensions (L x W x H):	483 x 140 x 136 mm
Max. Depth of Cut	30 mm

User benefits

- Paddle switch; Easy-to-hold slim grip achieved by optimised parts allocation
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Anti-restart function minimises accidental start-up
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft start for smooth start-ups
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

158237-4

Grip 36 complete

195354-9

Toolless Lock Nut M14, 180 - 230

412393-7 (2x)

Battery Cover For Xgt® Batteries

821552-6

Makpac case (4)

A-80656

Grinding Wheel 125 X 6 Mm, Wa36N,



191G06-2

Dust collecting cover set



347480-2

Wheel cover 125 mm



782423-1

Lock nut wrench 35



835E79-0

Inner tray (4)



Other

User manual

Parts drawing