



### Main

Range of product	Odace
Product or component type	LED
Product specific application	Replacement lamp
Type of packing	Plastic bag

### Complementary

Light source colour	White
Product destination	For Styl outer plate label holder
Fixing mode	Clip-in
Colour tint	White (RAL 9003)
Temperature rise	25 °C
Service life in hours	64000 h (L70) 55 lux
[Ue] rated operational voltage	250 V AC 50/60 Hz
Current consumption	8 mA
Number of cables	2
Material	ABS (acrylonitrile butadiene-styrene): support cover PC (polycarbonate): screen
Embedding depth	8.7 mm
Net weight	0.011 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC
Product certifications	N

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	28