

RS Pro 1 Output, Desktop Power Supply



Features:

- Input voltage range: 100 to 240VAC
- Power Consumption at no-load : 0.3W Max
- Energy efficiency Level VI
- Meets CE and UL standards
- LPS compliant
- Operating temperature: 0°C to 40°C
- Protections: short circuit/over load
- C8 input socket
- 2 year warranty

RS Stock No.		903-7109	903-7118	903-7111	903-7115	903-7124
Output	DC Voltage	5V	12V	15V	24V	48V
	Rated current	3A	1.5A	1.2A	0.75A	0.37A
	Current range	0-3A	0-1.5A	0-1.2A	0-0.75	0-0.37A
	Rated Power	15	18	18	18	18
	Line regulation	±2% max.				
	Ripple & Noise	<10%				
Input	Voltage range	100-264VAC				
	Frequency range	47-63Hz				
	Efficiency	81%				
Protections	Short circuit	Auto recovery				
	Overload	Auto recovery				

Mechanical Specification

