

## ECP-15 UK series 15W plug-in power supply



### Features

- x No load power consumption
- x Protections: short circuit//overload voltage//overload current
- x UK and European versions available
- x Compact and light-weight
- x Withstands operating environment of 0-40 C
- x Efficiencies up to 86%
- x 3 year warranty
- x External switch mode plug-top power supplies
- x Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- x Energy saving power supply
- x Class II double insulated
- x 1.2 metre (approx.) output lead with 2.1x5.5x9.5mm centre positive output connector
- x Regulated output
- x EMC compliance to EN 55022 Class B

| Part number | Voltage | Rated current | Voltage range  | Rated power | MTBF   |
|-------------|---------|---------------|----------------|-------------|--|
| 7262794     | 5V      | 3A            | 4.7 ~ 5.3V     | 15W         | 100,000hrs min.<br>MIL-HDBK –<br>217F (25°C) |
| 7262797     | 7.5V    | 2A            | 7.1 ~ 7.9V     |             |  |
| 7262791     | 9V      | 1.66A         | 8.5 ~ 9.5V     |             |  |
| 7262801     | 12V     | 1.25A         | 11.4 ~ 12.6V   |             |  |
| 7262804     | 15V     | 1A            | 14.25 ~ 15.75V |             |  |
| 7262808     | 18V     | 0.83A         | 17.1 ~ 18.9V   |             |  |
| 7262817     | 24V     | 0.62A         | 22.8 ~ 25.2V   |             |  |

### Mechanical specification

