

Price\* : 190.99 GBP



## Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	90 W
Input voltage	240 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

## Complementary

Operating position	Horizontal Vertical
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	External: 260 mm
Width	External: 440 mm
Depth	External: 1.6 mm
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By 4 screws
Mounting support	DIN rail Telequick mounting plate Adhesive Velcro Standard mounting plate

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---------------------------------------------------------------------------------------------------------------------------------------

---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--------------------------------------------------------------------------------------------------------

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---