

M8 D-cod 4-pol f PFT - RJ45 PUR 0.5M



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 B9B 6018 005
Specification	M8 D-cod 4-pol f PFT - RJ45 PUR 0.5M
HARTING eCatalogue	https://harting.com/0948B9B6018005

Identification

Category	System cabling
Series	Circular connectors M8
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M8 D-coding Female
Connector 2	RJ45
Type of cable	Copper cable (round)

Version

Cable length	0.5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-20 ... +70 °C
Cable diameter	6.5 mm

Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
Approvals	CE
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	52 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140570696
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600