

FEATURES

- Tested for 30,000 movements.
- Meets BS4533 Class 1 luminaire
- Polycarbonate lens
- Maximum lamp size ES 60W
- Rotatable anti-glare visor

RS PRO LED Retrofit Lamp Machine Light, 230 V, 60 W, Articulated, 830mm Reach, 750mm Arm Length

RS Stock No.: 600-723



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro, this bench task light is the ideal lighting system for those engaging in high concentration, high detail work. With an adjustable base, and an arm with four points of articulation, the operator can ensure there is bright, clear light source where it is needed. This has the advantage of ensuring shadow free work and reducing eye strain. With friction free joints, the arm adjusts easily and retains its position. It also has resistance to vibration, which means it is suitable for work around heavy machinery.

General Specifications

Lamp Type	Incandescent – self ballasted fluorescent – LED Retrofit Lamp
Light Style	Articulated Arm
Lamp Supplied	No
Integral transformer	No
Lamp Base	E27 Edison Screw
Base Type	Universal Base – can be horizontal or vertical mounted
Shield Fitted	No
Switch Fitted	Yes on head
Visor	Flexible visor fitted as standard (with retaining groove for shield)
Trailing Cable	Not fitted (available as accessory c/w 20mm cable gland)
Finish & Colour	Powder coated Goosewing Grey
Shade	127mm spun aluminium
Arm Type	Articulated

Electrical Specifications

Mains Plug Type	Euro plug , UK 3Pin Plug
Voltage Rating	240V
Wattage	60W
Number of Bulbs	1

Mechanical Specifications

Arm Length	750mm
Maximum Reach	830mm

Protection Category

IP Rating

IP 20



