
## KEMET Part Number: SSRH24NH-12655

(UALS24H1265500)



## KEMET, SSRH24NV/NH, AC Line Filters, Common Mode, 0.0655 H



General Information	
Series:	SSRH24NV/NH
Style:	Through-Hole
Features:	Compact Size, Light Weight, Low Rdc, Ultra-High Impedance
RoHS:	Yes
Miscellaneous:	65 (K) Temperature Rise Max.

Specifications	
Voltage AC:	250 VAC
Inductance:	65.5 mH (10 kHz)
Current:	1.2 A
Temperature Range:	-25/+120°C
DC Resistance:	475 mOhms

Dimensions		
L	25.5mm MAX	
т	25.5mm MAX	
Н	18mm MAX	
LL	3.5mm +/-0.5mm	
S	13mm NOM	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	300	
Weight:	22.5 g	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

