

Product information

MULTI TOOL



Satisfying the professional's needs

TM3000CX4

Oscillation Angle	3.2 °
Oscillations per Minute	6000 - 20000
Input Wattage	320 w
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Metal	3 m/sec ²
Vibration: Cutting Wood	6.5 m/sec ²
Vibration: Chiselling	5.5 m/sec ²
Vibration: Sanding	2.5 m/sec ²
Net weight	1.4 kg



STANDARD EQUIPMENT: 313248-8 UNIVERSAL ADAPTOR A, B-21325 SEGMENT SAW BLADE 85 TM006, B-21353 PLUNGE CUT SAW BLADE 28 TMA009, B-21434 PLUNGE CUT SAW BLADE 10 TMA017, B-21537 BACKING PAD- MULTI TOOL

- Thumb On/Off switch, positioned for ease of use when holding body of machine.
- Hex wrench holder on body.
- Variable speed control dial.
- Optional dust extraction attachment (Not included)
- Accessories can be installed at 30° increments, across 360°
- Uses OIS interface.

Details correct as of: 29-7-2015

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com