

## DWE1622K-QS

2 Speed 50mm Magnetic Drill Press



5035048402238



### Product Description :

Take on a variety of demanding applications with the 2 in. 2-Speed Magnetic Drill Press. Featuring a 10 Amp motor with 2 speed settings and overload protection, this tool helps you get tough jobs done fast.

### Product Features and Benefits :

- Overload protection with 3 stage LED indicator allows improved user control and prevents motor damage
- Push button reversible press handle offers tool-free handle set-up.
- Compact and light weight unit which is both easy to transport and easy to position for drilling.
- 2 mechanical speeds for Optimized performance
- No volt switch prevents inadvertent restart after power failure
- The universal quick release cutter holder is quick and easy to operate : no Allen key needed. It accepts any annular cutter with 19 mm round shank (Weldon) with one or more flats.
- Delivers high level of performance for fast, clean and accurate drilling into steel

### Technical specifications :

- Length of drill stroke [Metric] : 147 mm

### Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

### Product Applications :

Drilling applications with annular cutter up to 50mm in 50mm thick steel.

### Included items :

- 16mm Chuck & Adapter (x1)
- Quick Release Cutter Holder (x1)
- Gravity Fed Cutting Fluid Tank (x1)
- Safety Strap (x1)
- Heavy Duty Carrying Case (x1)
- Reversible Press Handle (x1)

**DWE1622K-QS**

2 Speed 50mm Magnetic Drill Press



5035048402238

Product from the series DWE1622K

Ref	Titre
DWE1622K-QS	2 Speed 50mm Magnetic Drill Press