

Previously known as: Sensilite®



Multi Purpose



Light Duty

White multi-purpose polyurethane gloves, designed with comfortable light duty handling in mind

- **Improved durability:** HyFlex® 48-100 industrial work gloves feature ANSI/ISEA and EN compliant abrasion resistance levels
- **Augmented dexterity:** Their thin, flexible nylon liner makes for dexterous, strain-free everyday use
- **White color:** The lighter tone of these HyFlex® gloves ensures process quality and helps avoid cross contamination
- **Optimized tactility:** HyFlex® 48-100 PPE gloves' palm-dipped PU coating results in high levels of tactile sensitivity, for precision handling in dry or slightly oily conditions
- **Genuine versatility:** Light, resilient and tactile, HyFlex® 48-100 industrial gloves are used for a multitude of diverse applications



Industries

- Automotive
- Machinery and Equipment

Applications

- Chassis assembly, body trimming
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Loading and unloading rough parts or boxes
- Picking parts and accessories

HyFlex®

ADVANCED MECHANICAL PROTECTION

48-100

Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite®

Key Features

- **Palm-dipped PU coating:** ANSI/ISEA and EN compliant abrasion resistance
- **Thin nylon liner:** Dexterous comfort for light-duty applications
- **White color:** Process safe PPE gloves that avoid cross contamination

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



4131A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 48-100	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	210 - 265 mm/ 8.27-10.43 inches	White	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

