




LOC		DIST		REVISIONS					
FT		O		P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER ECO-12-015521			28SEP12	KH	MZ

D



C



DETAIL A



B



DETAIL B

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT THIRTY-SEVEN (37) MULTIMATE SOCKET CONTACTS.
- 3 NO 4 FASTENER RECOMMENDED FOR MOUNTING.
- 4 NYLON 6/6, NATURAL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE 5	STANDARD	NO	3.81 [.150] DIA HOLE	A	4 206306-8
	SMALL PACK	NO	3.81 [.150] DIA HOLE	A	206306-6
	STANDARD	NO	4-40 THREADED INSERT	A	206306-5
	STANDARD	YES	-	B	206306-4
	STANDARD	YES	3.81 [.150] DIA HOLE	A	206306-3
	STANDARD	NO	-	B	206306-2
	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-1
	PACKAGING	PERIPHERAL SEAL	C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 07/26/93	TE Connectivity		
		CHK R.STONE 08/11/93			
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME A.FRANTUM 08/13/93	RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC	
		0 PLC ± -	PRODUCT SPEC 108-10024	SIZE A1	
		1 PLC ± -	APPLICATION SPEC	CAGE CODE 00779	
MATERIAL HOUSING: NYLON, BLACK INSERT: BRASS		2 PLC ± 0.13 [.005]	WEIGHT -	DRAWING NO 206306	
		3 PLC ± -	CUSTOMER DRAWING		RESTRICTED TO -
		4 PLC ± -	SCALE 2:1		SHEET 1 OF 1
		ANGLES ± -	REV L		