

### Main

Range	New Unica
Device application	Mounting
Product or component type	Mounting box
Number of modules	2 x 8 modules
Fixing mode	Screws




### Complementary

Device mounting	Surface
Cable entry	5 removable plates 2 bottom cable entries 30 mm for diameter 2 bottom cable entries 20 mm for diameter 2 bottom cable entries 25 mm for diameter
Material	ABS (acrylonitrile butadiene-styrene): box ABS (acrylonitrile butadiene-styrene): separator PC: tower
Depth	50 mm
Width	230 mm
Height	165 mm
Net weight	0.31 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

IK degree of protection	IK04
-------------------------	------

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>