

Product data sheet

Characteristics

KBD1H

operating head 60 x 60 mm - metallic color -
black handle - blank for engraving



Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KBD
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole
Cam switch head type	With front plate 60 x 60 mm
Type of operator	Black handle, length = 42 mm
Rotary handle padlocking	Without
Presentation of legend	With metallic legend

Complementary

Mechanical durability	1000000 cycles
CAD overall width	60 mm
CAD overall height	60 mm
CAD overall depth	77 mm
Length	42 mm
Net weight	0.053 kg
Compatibility code	KBD

Environment

Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------