

### **FEATURES**

- Dual voltage thermostat
- Mechanical device
- Supply voltage of 230 V and 24 V
- Temperature range of +5°C to +35°C
- EU Directives 2011/65/EU and 2015/863 compliant for safety

# RS PRO Thermostats, +5 → +35 °C

RS Stock No.: 719-4143



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



## **Product Description**

Looking for a simple way to adjust the climate of your indoor environment? This RS PRO dual-voltage thermostat lets you control your ambient temperature in a range of +5°C to +35°C.

Found in a wide range of domestic and commercial environments – from shops and offices to garages and workshops – this thermostat has an uncomplicated white interface with an adjustable, rotating control dial and easy-to-read, grey numbered markings. You'll find a handy wall mount on the back of the device to make installation as simple as possible. It can be powered by either an electricity mains supply of 230 V or a battery supply of 24 V.

#### **General Specifications**

Product Type	Dual voltage thermostat
Temperature Range	+5°C to +35°C
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Additional Features	Dual voltage thermostat, Mechanical device
Applications	Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security

# **Electrical Specifications**

Supply Voltage	230V
Battery	24V
Operation	Turn

#### **Approvals**

Compliance/Certifications	RoHS (Restriction of Hazardous Substances) compliant, ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007,
	2011/65/EU and 2015/863







