

Datasheet

DIN Connector Socket

RS Stock number 811-8225



Specifications:

| | |
|--------------------------------------|--|
| Connection Type: | 2Pole + Earth |
| Voltage: | 250V AC |
| Approvals: | N.A. |
| Standard: | N.A. |
| Mounting: | Screw-type |
| Type: | MEM -Socket (Micro DIN Connector) – Non-illuminated |
| Socket Type: | Type C |
| Mounting: | M3 Screw |
| Material For Rubber Gasket: | Nitril / Silicon |
| Material Body: | Nylon-6 GF |
| Gland Size: | PG-7 |
| Body Colours: | Black / Grey |
| Contact Resistance (Initial): | 20 m Ohms max. |
| Current Carrying Parts: | Copper Alloy, Tin plated |
| Permissible Temp. With/Without Load: | 0°C to 90°C |
| Rating: | 6A, 250VAC |
| Terminals: | Screw-type |
| H. V. Breakdown Test: | 2 KV AC For 1 Minute. |
| Insulation Resistance: | 100 M Ohms min. |

Unit mm

