

Pliers for Electrical Installation

The mobile task force.



13 82 200



13 86 200



13 92 200



13 96 200



- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping end sleeves (ferrules)
- 6 functions in one pair of pliers
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the jaw for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.7 - 1.5 mm² and 2.5 mm²
- Crimp die for wire-end ferrules 0.5 - 2.5 mm²
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm² / dia. 5 mm
- Gripping, without opening the pliers completely
- Intelligent latching mechanism in the spring assisted version
- The cutting edge remains closed and protected
- Slim dimensions for easy access
- Joint with screw: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, oil-hardened

Model 13 92 / 96 200 :

- The activated locking lever keeps the cutting edges closed while other functions remain in place
- The intelligent latching mechanism enables you to "grip" without opening the pliers. The cutting edge remains closed and protected.



No.	EAN 4003773-	Ø mm	mm ²	Stripping capacity for cross-sections mm ²	Capacity mm ²	mm	g
13 82 200	075080	15	50	0,7 - 1,5 + 2,5	0,5 - 2,5	200	280
13 86 200	075097	15	50	0,7 - 1,5 + 2,5	0,5 - 2,5	200	280
13 92 200	075103	15	50	0,7 - 1,5 + 2,5	0,5 - 2,5	200	280
13 96 200	075110	15	50	0,7 - 1,5 + 2,5	0,5 - 2,5	200	280