



Rapid BNX50 – 18V Battery Nailer

High quality cordless brad nailer offering optimal freedom of movement and performance. BNX50 brad nailer lets the user avoid complicated gas-driven or pneumatic solutions. Ideal for fitting skirting board, architrave and window trim, tongue and groove paneling.

Features:

- LED work light
- Adjustable depth-of-drive
- Soft tip to protect working material
- Both single or "bump" fire modes
- Tool-free jam clearing hinge in front
- Belt hook included
- Up to 600 shots per charge (2.5 Ah battery)
- 2-year guarantee

Specification:

- For 18-gauge brads Rapid No8, 20-50 mm
- Supplied in box (bare tool) or in Showcase (incl. battery & charger)



No cable. No limits. One single battery for all your tools. The Bosch POWER FOR ALL ALLIANCE battery offers the greatest application variety for home users in the market.



Description

BNX50 18V Brad Nailer

Packaging

Showcase EU

Art. No

5001498

EAN

4051661037597

Packaging unit

3 pcs/outer