

P1.5-23VSC



Vinyl-Insul 0.5-1.5 PIN TERM 23MM



General Information

Extended Product Type	P1.5-23VSC
Product ID	7TCA301300R0196
EAN	5415022405491
Catalog Description	Vinyl-Insul 0.5-1.5 PIN TERM 23MM
Long Description	Vinyl-Insulated Pin Terminal, Single Crimp, Length 23mm, Width 1.9mm, Diameter 1.7mm, Wire Range 0.5-1.5mm ² , Copper, Tin Plated, 600V Max, Temperature Rating 75 Degrees Celsius

Ordering

EAN	5415022405491
Minimum Order Quantity	100 piece
Customs Tariff Number	8536699000

Dimensions

Product Net Weight	0.721 g
--------------------	---------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	25.4 mm
Package Level 1 Height	119.888 mm
Package Level 1 Depth / Length	149.86 mm
Package Level 2 Units	2200 piece
Package Level 2 Width	180.086 mm
Package Level 2 Height	150.114 mm
Package Level 2 Depth / Length	89.916 mm
Package Level 3 Units	22000 piece
Package Level 3 Width	320.04 mm
Package Level 3 Height	199.898 mm
Package Level 3 Depth / Length	480.06 mm

Additional Information

Brand / Label	Spec-Kon
Material	Copper

Product Main Type	COMPRESSION TERMINALS
Product Name	OTHER SWITCHES
Product Type	Vinyl-Insulated Pin Terminal
UPC	786210140100

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	P1.5-23VSC
Instructions and Manuals	P1.5-23VSC

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

