

PRO Router Bit Mixed Set, 15 pcs

PRO



- ▶ For all essential routing tasks in softwood, hardwood, and composite wood
- ▶ Highly efficient for cabinet makers, joiners, and carpenters: Precision
- ▶ Designed for routing wood
- ▶ Cylindrical shank compatible with routers



PRODUCT PROPERTIES										ORDERING INFORMATION				Barcode	Part number
Shank mm	Shank inch	Diameter (D) mm	Radius (R1) mm	Working length (G) mm	Total length (G) mm	Diameter (D) Inch	Radius (R1) Inch	Working length (G) Inch	Total length (G) Inch	Angle degrees	Packaging type	Pack quantity	Minimum order quantity		
Flush trim bit (1x); Flush pattern bit (1x); Dovetail bit (1x); Chamfer bit (2x); V-groove bit (1x); Slotting cutter (1x); Rebating bit (1x); Roman ogee bit (1x); Cove bit (1x); Rounding over bit (2x); Straight bit 2-cutter (2x); Straight bit 3-cutter (1x)															
6	-	13	-	25	65	-	-	-	-	-	P1k	15	1	3165140958028	2 607 017 471
	-	16	-	25	65	-	-	-	-	-					
	-	13	-	12	49	-	-	-	-	12					
	-	35	-	16	56	-	-	-	-	45					
	-	25	-	13	54	-	-	-	-	25					
	-	16	-	18	50	-	-	-	-	60					
	-	32	-	4	50	-	-	-	-	-					
	-	32	-	13	54	-	-	-	-	-					
	-	27	4	12	52	-	-	-	-	-					
	-	29	10	12	54	-	-	-	-	-					
	-	19	3	10	51	-	-	-	-	-					
	-	25	6	13	55	-	-	-	-	-					
	-	8	-	20	50	-	-	-	-	-					
	-	10	-	30	60	-	-	-	-	-					
	-	16	-	30	60	-	-	-	-	-					
8	-	13	-	25	65	-	-	-	-	-	P1k	15	1	3165140958035	2 607 017 472
	-	16	-	25	65	-	-	-	-	-					
	-	13	-	12	49	-	-	-	-	12					
	-	35	-	16	56	-	-	-	-	45					
	-	25	-	13	54	-	-	-	-	25					
	-	16	-	18	50	-	-	-	-	60					
	-	32	-	4	50	-	-	-	-	-					
	-	32	-	13	54	-	-	-	-	-					
	-	27	4	12	52	-	-	-	-	-					
	-	29	10	12	54	-	-	-	-	-					
	-	19	3	10	51	-	-	-	-	-					
	-	25	6	13	55	-	-	-	-	-					
	-	8	-	20	50	-	-	-	-	-					
	-	10	-	30	60	-	-	-	-	-					
	-	16	-	30	60	-	-	-	-	-					